







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/






- Specifications()
- 1.Voltage rating():1500V DC
 - 2.Current rating():350A MAX
 - 3.Withstanding voltage():6800V DC
 - 4.Insulation resistance():200MΩ at DC1500V
 - 5.Protection level():IP67
 - 6.Mating cycles 500 cycles Min
 - 7.Temperature range():-40 ~+125



KES-007 W V-M8 B

H6=φ6
B0=M10
M6=M6 ()
M8=M8 ()

A:A
B:B



Ra3.2 0.2

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KES-007WV-M8B
APPROVED		SIZE: A4	DWG NO.: