




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术要求(Technical Index):

1. 材质与表面处理(Material And Finish):
基座 (Housing) and 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal) :Phosphor Copper Au/Sn Plated;
焊片 (Solder) : Copper Alloy Au/Sn Plated;
2. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压(Withstanding Voltage): 200V AC/minute.

40PIN



CUSTOMER DRAWING				LAILIAN 深圳市莱联电子有限公司								
DRAWING				SHENZHEN LAILIAN ELECTRONICS CO.,LTD								
CHECKED												
APPROVED												
TOLERANCES ARE				TITLE		FPC连接器0.5间距40PIN抽屉式上接（焊贴）		REV.		A		
30-150		±0.35		ANGLE	PART NO.		LAIL-FPC-BS01-40P0.5-W		UNITS		mm	
10-30		±0.2			DWG. NO.				Projection 			
5-10		±0.15										
0-5		±0.1										
		±3°										