





- NOTE:
- 1.Rating1: 3A 125VAC 1.5A 125/250VAC
 - 2.Contact resistance: 500mΩ MAX
 - 3.Insulation Resistance: 100MΩ MIN DC500V
 - 4.Withstand Voltage: AC500V 1min
 - 5.Electrical Life:10,000 cycles
 - 6.Mechanical Life:1000,000 cycles
 - 7.Operating Force: 30±15gf
 - 8.Waterproof: IPX7

⑨	Handle	—	1	SUS	—	—
⑧	Waterproof Hat	—	1	Silicone Rubber	—	—
⑦	Waterproof Cap	—	1	Silicone Rubber	—	—
⑥	Shrapnel	—	1	Phosphor bronze	Plating silver	—
⑤	Contact	—	3	Silver alloy	—	—
④	Terminal	—	3	Brass(0.50t)	Plating silver	—
③	Button	—	1	PBT	White	—
②	Case	—	1	PBT	Black	—
①	Cover	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE			
DRAWN	LIANG		2026.07.06			
CHECKED				TITLE:	MICRO SWITCHS	
APPROVALS				PART NO.	K9-2933K-DDBB	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20		DRAWING NO.		SHEET 1 OF 1
	5~10	±0.15				
	~ 5	±0.10	±2'			

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.