








PCB Layout(Pattern side)



左弯脚



Circuit Diagram



NOTE:
Rating: DC 30V 100mA
Operating Force: 50gf Max
Electrical Life: 300,000 Cycles
Mechanical life: 300,000 Cycles

⑦	Touch Point	—	1	Silver Alloy	Natural	—
⑥	Spring Plate	—	1	Beryllium copper	Natural	—
⑤	Terminal	—	3	Brass	Ag Plated	—
④	Housing	—	1	Nylon	Black	—
③	Cover	—	1	PBT	Grey	—
②	Knob	—	1	PBT	White	—
①	Lever	—	1	SUS	Natural	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE							
DRAWN		LIUCAN	2023.8.13							
CHECKED				TITLE:		MICRO SWITCHS				
APPROVALS				PART NO.		K9-8227Y-L3DN-2G				
TOLERANCES ARE		30以上	±0.30	ANGLE	UNIT: mm		SCALE: 1:1		PROJ: 	
		10~30	±0.20							
		5~10	±0.15							
		~ 5	±0.10							
				±2'	DRAWING NO.				SHEET 1 OF	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			