





SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:−40°to+105°



Insrlator Material:Polyester(UL94V-0)

Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30–60seconds
(260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM1.0-1-1PU-W	1	0.00	1.00
BX-PM1.0-1-2PU-W	2	1.00	2.00
BX-PM1.0-1-3PU-W	3	2.00	3.00
BX-PM1.0-1-4PU-W	4	3.00	4.00
BX-PM1.0-1-5PU-W	5	4.00	5.00
BX-PM1.0-1-6PU-W	6	5.00	6.00
BX-PM1.0-1-7PU-W	7	6.00	7.00
BX-PM1.0-1-8PU-W	8	7.00	8.00
BX-PM1.0-1-9PU-W	9	8.00	9.00
.....			
BX-PM1.0-1-20PU-W	20	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PM1.0-1-NPU-W	版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA			品名 TITLE	1.0FH H2.0 1xnPin SMT W1.5 U 2.8 PB2.3 6T (左端后)	页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1				