




NOTE:
1.Rating: 5A 125/250VAC
2.Operating force: 100gf Max
3.Differential travel:0.7mm Max
4.Over travel:0.6mm Min
5.Electric Life:50,000
6.Mechanical Life:500,000
7.Ingress protection:IP67

⑧	Handle	—	1	SUS	—	—
⑦	Shrapnel	—	1	Brass	Plating silver	—
⑥	Contact	—	1	Ag	—	—
⑤	Sealed Circle	—	1	Silicone Rubber	—	—
④	Terminal	—	3	Brass(0.50t)	Plating silver	—
③	Plunger	—	1	POM	Black	—
②	Case	—	1	PA	Black	—
①	Cover	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK


APPROVALS			DATE		 hro®	
DRAWN		LIUCAN	2023.10.8			
CHECKED					TITLE: MICRO SWITCHES	
APPROVALS					PART NO. K9-2891A-WB1B	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10				
			±2'	DRAWING NO.	_____	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			


K9-2891选型表


K9-2891N-XC1B

开关系列	名称
K9	防水微动开关

编码	图示	产品规格
9		20.0*6.5*9.3

编码	额定负载
1	5A 125/250V AC

编码	手柄类型
A	 01
B	 02
C	 03
N	无手柄

编码	端子类型	编码	端子类型
H		X	
W		Y	

编码	线材长度L	编码	线材长度L
0	无线材省略	C	250mm
A	150mm	D	300mm
B	200mm	其它	...

流水号	电线规格	流水号	电线规格
0	无线材省略	5	0.14mm2*6C
1	UL1007 22AWG美标	6	UL1007 24AWG美标
2	AVSS0.3日标	7	特氟龙24AWG
3	AVSS0.5日标	8	VW-1 1015 20AWG
4	UL1007 20AWG美标	9	UL2468 24AWG VW-1 80℃

编码	触点类型
D	常开/常闭 SPDT
B	常开 SPST-NO
C	常闭 SPST-NC