






Circuit Diagram



PCB Layout(Pattern side)

NOTE:
Rating: DC 30V 100mA
Operating Force: 50gf Max
Lifetime: 20,000 Cycles



⑦	Touch Point	—	1	Silver Alloy	Natural	—
⑥	Spring Plate	—	1	Beryllium copper	Natural	—
⑤	Terminal	—	3	Brass	Ag Plated	—
④	Housing	—	1	Nylon	Black	—
③	Cover	—	1	PBT	Black	—
②	Knob	—	1	PBT	White	—
①	Lever	—	1	SUS	Natural	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIUCAN	2023.5.22				
CHECKED							
APPROVALS							
			TITLE:		MICRO SWITCHS		
			PART NO.		K9-8227Y-D3DA-1B		
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm	
			10~30	±0.20			
			5~10	±0.15			
			~ 5	±0.10			
			±2'		DRAWING NO.	_____	PROJ: 
					SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			