



ROHS





REV.	ECN NO.	DESCRIPTION	DRAW	DATE

10PIN

技术指标 (Technical Index):

1. 塑件材质: LCP UL94-V0
2. 端子材质: 磷青铜, 镀锡/镀金
3. 焊片材质: 磷青铜, 镀锡/镀金
4. 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
5. 额定电压 (Rated voltage): 50V, AC/DC (=等效).
6. 接触电阻 (Contact resistance): $\leq 0.03\Omega$.
7. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.
8. 耐压: 200V/1 Minute.



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED			
APPROVED			
TOLERANCES ARE		TITLE	FPC连接器0.5间距10PIN抽屉式单侧触点/垂直(立贴)
30-150	±0.35	PART NO.	LAIL-FPC-BL01-10P0.5-LT
10-30	±0.2	DWG. NO.	
5-10	±0.15		
0-5	±0.1		
ANGLE		UNITS	mm
±3°		Projection	