









- 技术要求Notes:
- 1.外观质量Appearance quality:
 - a.金属表面镀层不能有明显损伤;
 - b.塑壳表面不能有明显的变形或开裂;
 - c.产品表面应保持清洁;
 - 2.工作温度 Working temperature: -25℃~+105℃;
 - 3.额定电压 Voltage Rating : Max 50V [AC(Effective value rms)/DC];
 - 4.额定电流 Current Rating: Max 1A [AC(Effective value rms)/DC];
 - 5.接触电阻 Contact resistance: Max 20 mΩ
 - 6.绝缘电阻 Insulation resistance: Min 100MΩ;
 - 7.耐压 Withstanding voltage: 500V AC(50 Hz, Effective value: 1 min);
 - 8.环保要求应符合RoHS标准
- Environmental requirements should meet RoHS standards.

3	焊片Fitting Nail	磷铜 Phosphor copper	2	镀锡 Tin-plated
2	端子Terminal	磷铜 Phosphor copper	N	镀锡 Tin-plated
1	基座Housing	LCP UL94-V0	1	本色Natural color
序号 No.	名称 Part Name	材料 Material	数量 Qty	备注 Remark

16	18.75	23.25	21.25	6.5
15	17.50	22.00	20.00	6.5
14	16.25	20.75	18.75	6.5
13	15.00	19.50	17.50	6.5
12	13.75	18.25	16.25	6.5
11	12.50	17.00	15.00	6.5
10	11.25	15.75	13.75	6.5
9	10.00	14.50	12.50	4.5
8	8.75	13.25	11.25	4.5
7	7.50	12.00	10.00	4.5
6	6.25	10.75	8.75	4.5
5	5.00	9.50	7.50	3.25
4	3.75	8.25	6.25	2.00
3	2.50	7.00	5.00	1.75
2	1.25	5.75	3.75	0.5
孔位 GKT NO.	DIM A	DIM B	DIM C	DIM D

APPROVALS		DATE	
DRAWN	G.M.Chen	2015/7/17	
CHECKED			
APPROVALS			
TOLERANCES ARE		30~0.15	±0.30
		10~0.10	±0.20
		5~0.05	±0.15
		±2°	ANGLE
PART NO.		L125WS-XXPS	
TITLE:		GH1.25mm Pitch Vertical SMT Connector	
DRAWING NO.		SHEET 1 OF 1	
PROJ.			

ECN NO.

REV.

DATE.

DESCRIPTION.

CHANGE.

CHECK.

APPRO.