










REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/

 for 16A for 16B for 17A DIM.A 12.00 14.10 3PCS		 for 16A for 16B for 17A DIM.A 10.50 11.70 13.80 3PCS		 for 16A for 16B for 17A DIM.A 8.60 11.40 3PCS	
---	--	---	--	--	--



- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():80A
 - 3.Withstanding voltage():3000V AC 1Min, 5mA MAX
 - 4.Insulation resistance():≥200MΩ at DC1000V
 - 5.Shield():360°
 - 6.Protection level():IP67
 - 7.Recommended screw torque():M4 1.5~2.0N.m
 - 8.Temperature range():-40 ~+125

KCT-125-16A

16A=16mm² OD=9.5~10.4mm
250=25mm² OD=12.6~13.6mm
16B=16mm² OD=10.9~11.7mm

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW: 	MODEL TYPE: A 2
CHECKED		UNIT: mm/in	PART NO.: KCT-125-16A
APPROVED		SIZE: A4	DWG NO.: