












REVISIONS																					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN																
A0	N/A		INITIAL RELEASE	2025.11.03																	
/	N/A		/	/	/																
																					
<table><tr><td></td><td>for16A</td><td>for16B</td><td>for17A</td></tr><tr><td>DIM.A</td><td>12.00</td><td>14.10</td><td></td></tr></table>				for16A	for16B	for17A	DIM.A	12.00	14.10		<table><tr><td></td><td>for16A</td><td>for16B</td><td>for17A</td></tr><tr><td>DIM.A</td><td>10.50</td><td>11.70</td><td>13.80</td></tr></table>				for16A	for16B	for17A	DIM.A	10.50	11.70	13.80
	for16A	for16B	for17A																		
DIM.A	12.00	14.10																			
	for16A	for16B	for17A																		
DIM.A	10.50	11.70	13.80																		
3PCS			3PCS																		
			<table><tr><td></td><td>for16A</td><td>for16B</td><td>for17A</td></tr><tr><td>DIM.A</td><td>8.60</td><td>11.40</td><td></td></tr></table>				for16A	for16B	for17A	DIM.A	8.60	11.40									
	for16A	for16B	for17A																		
DIM.A	8.60	11.40																			
			3PCS																		

					
Specifications() 1.Voltage rating():1000V DC 2.Current rating():80A 3.Withstanding voltage():3000V AC 1Min, 5mA MAX 4.Insulation resistance():≥200MQ at DC1000V 5.Shield():360° 6.Protection level():IP67 6.5mm IP67 7.Recommended screw torque():M4 1.5~2.0N.m 8.Temperature range():-40 ~+125					
KCT-134-16A 16A=16mm² OD=9.5~10.4mm 250=25mm² OD=12.6~13.6mm 16B=16mm² OD=10.9~11.7mm					

	DESIGN		VIEW: 	MODEL TYPE: A 3		
	CHECKED		UNIT: mm/in	PART NO.: KCT-134-16A		
	APPROVED		SIZE: A4	DWG NO.:		
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1	REVISION A0