


ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术要求 (Technical Index):



1. 材质与表面处理 (Material And Finish):
基座 (Housing) 和 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
2. 工作温度 (Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压 (Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压 (Withstanding Voltage): 200V AC/minute.




6PIN



SECTION A-A



PCB LAYOUT



COSTOMER DRAWING		深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING		TITLE		FPC连接器1.0间距6PIN翻盖下接H2.0 卧贴	REV.	A
CHECKED						
APPROVED						
TOLERANCES ARE		PART NO.	LAIL-FPC-CX01-6P1.0-W	UNITS	mm	
30-150	±0.35					ANGLE
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±0.3	DWG. NO.		Projection	