

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: -55°C~+85°C.


OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: -10°C~+50°C.





STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE >500MΩ.

WITHSTAND VOLTAGE: 200V/1 MINUTE.



10PIN



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	FPC连接器0.5间距10PIN翻盖式双侧触点上下接	REV.	A
30-150	±0.35	PART NO.	LAIL-FPC-CDX01-10P0.5-GW	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG. NO.		Projection	
±3°					