




ROHS





PCB Layout

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

30PIN

技术指标(Technical Index):

1. 塑件材质: LCP UL94-V0
2. 端子材质: 磷青铜, 镀锡/镀金
3. 焊片材质: 磷青铜, 镀锡/镀金
4. 温度范围(Temperature range): -25° C~85° C.
5. 额定电压(Rated voltage): 50V, AC/DC(=等效).
6. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
7. 绝缘电阻(Insulation resistance): $\geq 500M\Omega$.
8. 耐压: 200V/1 Minute.



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	FPC连接器0.5间距30PIN抽展式单侧触点/垂直(立贴)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-FPC-BL01-30P0.5-LT	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					