







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



Specifications()
1.Voltage rating():1500V DC
2.Current rating():200A MAX
3.Withstanding voltage():6800V DC
4.Insulation resistance():200MQ at DC1500V
5.Protection level():IP67
6.Mating cycles 500 cycles Min
7.Temperature range():-40 ~+125



KES-004 W V-M6 B

H5=φ5
B8=M8
M5=M5 ()
M6=M6 ()

A:A
B:B

Ra3.2 0.2.

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KES-004W-M6B
APPROVED		SIZE: A4	DWG NO.: