




REVISONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



Specifications()

1.Voltage rating():1000V DC

2.Current rating():25A(2.5mm²)
35A(4mm²)
40A(6mm²)

3.Withstanding voltage():3000V AC,1min ≤2mA

4.Insulation resistance():200MΩ at DC1000V

5.Protection level():IP67

6.Mating cycles 200 cycles Min

7.Salt spray test 5% NaCl 48H;

8.Temperature range():-40 ~+125

9.Recommended screw torque() M3:0.8~1.0N.m()

KLV-322 W V-2A X B

2A=2.5mm²
04=4mm²
06=6mm²

B:
S:
X:X
Y:Y
U:U

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 3 4mm
CHECKED		UNIT: mm/in	PART NO.: KLV-322WV-2AXB
APPROVED		SIZE: A4	DWG NO.:
SCALE			PAGE
N/A			1/1
REVISION			A0