








REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/




- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():150A (35);
 - 3.Withstanding voltage():3000V AC 1Min, 2mA MAX
 - 4.Insulation resistance():200MΩ MIN at DC1000V
 - 5.Protection level():IP67
 - 6.Mating cycles 100 cycles Min
 - 7.Salt spray test 5% NaCl 48H;
 - 8.Temperature range():-40 ~+125

KHV-220 E V-35 A S

35=35mm²(OD:Ø14.50±0.50mm)

A:A
B:B
C:C



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:	MODEL TYPE: 2
CHECKED		UNIT: mm/in	PART NO.: KHV-220FV-35AS
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A0