













REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



ØA	ØB	
2.40	4.00	2.5
3.00	4.80	4
3.60	6.00	6
4.90		10

- Specifications()
- Voltage rating():1000V DC
 - Current rating():25A(2.5mm²)
35A(4mm²)
45A(6mm²)
60A(10mm²)
 - Withstanding voltage():3000V AC,1min ≤2mA
 - Insulation resistance():200MΩ at DC1000V
 - Protection level():IP67
 - Mating cycles 200 cycles Min
 - Salt spray test 5% NaCl 48H;
 - Temperature range():-40 ~+125
 - Recommended screw torque() M3:0.8~1.0N.m()

KLV-221 W V-06 X S

2A=2.5mm²
04=4mm²
06=6mm²
10=10mm²

B:
S:
X:X
Y:Y
U:U
V=V

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2 4mm
CHECKED		UNIT: mm/in	PART NO.: KLV-221WV-06XS
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A0