








[Http://www.krthro.com](http://www.krthro.com)




PCB LAYOUT (TOP VIEW)
TOLERANCE: ± 0.05



Ø3.50mm 4 POLE PLUG DETAIL



Ø3.50mm 4 POLE PLUG SCHEMATIC



SCHEMATIC

Rating:0.5A 30V DC
Contact Resistance:100 mΩ Max.
Operating temperature:-25℃~80℃
Operating force:3-30N
Operating Life:5,000cycles

②	Shunt terminal	_____	6	Phosphor bronze	Plating Au	_____
①	Housing	_____	1	PPA	Black	_____
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE		 hro®		
DRAWN	LIUCAN	2023.3.16				
CHECKED						
APPROVALS						
			TITLE:	PHONE JACKES		
			PART NO.	PJ-332B-6A		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10				
			DRAWING NO.	SHEET 1 OF		

							CHECKED				TITLE:	PHONE JACKES		
							APPROVALS				PART NO.	PJ-332B-6A		
	A		NEW				TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.		10~30	±0.20		±2'	DRAWING NO.		SHEET 1 OF
								5~10	±0.15					
								~ 5	±0.10					