







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术要求(Technical Index):

1. 材质与表面处理(Material And Finish):
基座 (Housing) and 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal) :Phosphor Copper Au/Sn Plated;
焊片 (Solder) : Copper Alloy Au/Sn Plated;
2. 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压(Withstanding Voltage): 200V AC/minute.

24PIN



适用扁平电缆

COSTOMTER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECKED							
APPROVED							
TOLERANCES ARE							
30-150	±0.35	ANGLE	TITLE		FPC连接器0.5间距24PIN抽屉式上接（卧贴）	REV.	A
10-30	±0.2		PART NO.		LAIL-FPC-BS01-24P0.5-W	UNITS	mm
5-10	±0.15		DWG. NO.			Projection	
0-5	±0.1						
					±3°		