






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/





- Specifications()
- Voltage rating():1000V DC
 - Current rating():25A(2.5mm²)
35A(4mm²)
45A(6mm²)
60A(10mm²)
 - Withstanding voltage():3000V AC,1min ≤2mA
 - Insulation resistance():200MΩ at DC1000V
 - Protection level():IP67
 - Mating cycles 200 cycles Min
 - Salt spray test 5% NaCl 48H;
 - Temperature range(): -40 ~+125

KLV-213 W V-04 X B

2A=2.5mm²
04=4mm²
06=6mm²
10=10mm²

B:
S:
X:X
Y:Y
U:U
V=V



φA	φB	
2.40	4.00	2.5
3.00	4.80	4
3.60	6.00	6
4.90		10

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: A 2 4mm
CHECKED		UNIT: mm/in	PART NO.: KLV-213WV-04XB
APPROVED		SIZE: A4	DWG NO.: