







NOTE:

1. Rating: DC 30V 0.1A.
2. Contact resistance: 100mΩ Max.
3. Insulation resistance: 100MΩ Min(at DC 500V)
4. Withstand voltage: AC 500V for 1 minute
5. OP: 3.3±0.2mm.
6. Operating force: 90gf Max & 150gf Max.
7. Mechanical Life: 5,000,000 & 1,000,000.
8. Operating temperature: -25°C to 70°C

PART NO	vigor(gf)	Mechanical Life
K9-8601B-01	90gf Max	5,000,000
K9-8601B-02	150gf Max	1,000,000



⑥	Terminal	—	2	Brass	Plating silver	—
⑤	Contact	—	1	Silver alloy	—	—
④	Knob	—	1	Nylon	White	—
③	Cover	—	1	Nylon	Black	—
②	Leaf spring	—	1	Beryllium copper	—	—
①	Housing	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE					
DRAWN		LIUCAN	2022.11.24					
CHECKED					TITLE:		MICRO SWITCH	
APPROVALS					PART NO.			
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	SHEET 1 OF 1	
	10~30	±0.20						
	5~10	±0.15						
	~ 5	±0.10						
		±2'	DRAWING NO.					

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.