









NOTE:
1.Rating: DC 12V 0.05A
2.Contact resistance: 100mΩ MAX
3.Insulation Resistance: 100MΩ MIN
4.Dielectric Strength: AC 250V(50~60Hz)/60S
5.Operating Force: 180gf±50gf
6.Mechanical Life: 30,000 Cycles
7.Practical Temperature Rang: -40℃~+85℃
8.SOLDERING, SWITCH IS UNLOCK

NO.	Operating Type	Part No.
1	Push To Lock	K8-5852G-L1
2	Push No Lock	K8-5852G-N1

⑦	TERMINAL	—	6	BRASS	Ag PLATED	—
⑥	CASE	—	1	PPA	GRAY	—
⑤	LOCK PIN	—	1	SUS WIRE	NATURAL	—
④	SPRING	—	1	SUS WIRE	NATURAL	—
③	CONTACT	—	2	BRONZE	Ag PLATED	—
②	KNOB	—	1	PPA	WHITE	—
①	COVER	—	1	PPA	BLACK	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®		
DRAWN	LIANG	2026.07.20					
CHECKED				TITLE:	PUSHBUTTON SWITCHS		
APPROVALS				PART NO.			
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'	DRAWING NO.			SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			