





技术要求Notes:

- 外观质量Appearance quality:
 - 金属表面镀层不能有明显损伤: Coating on metal surface can not be damaged obviously;
 - 塑壳表面不能有明显的变形或开裂; No obvious deformation or cracking can be observed on the surface of the Housing;
 - 产品表面应保持清洁;

- Product surface should be kept clean;
- 工作温度 Working temperature: -25℃~+105℃;
 - 额定电压 Voltage Rating : Max 50V [AC(Effective value rms)/DC];
 - 额定电流 Current Rating : Max 1A [AC(Effective value rms)/DC];
 - 接触电阻 Contact resistance: Max 20 mΩ
 - 绝缘电阻 Insulation resistance: Min 100MΩ;
 - 耐压 Withstanding voltage: 500V AC(50 Hz, Effective value: 1 min);
 - 环保要求应符合RoHS标准
- Environmental requirements should meet RoHS standards.



序号 No.	名称 Part Name	材料 Material	数量 Qty	备注 Remark
3	焊片Fitting Nail	磷铜 Phosphor copper	2	镀锡Tin-plated
2	端子Terminal	磷铜 Phosphor copper	N	镀锡Tin-plated
1	基座Housing	LCP UL94-V0	1	本色Natural color

孔位 CKT NO.	DIM A	DIM B	DIM C	DIM D
16	18.75	23.25	21.25	6.5
15	17.50	22.00	20.00	6.5
14	16.25	20.75	18.75	6.5
13	15.00	19.50	17.50	6.5
12	13.75	18.25	16.25	6.5
11	12.50	17.00	15.00	6.5
10	11.25	15.75	13.75	6.5
9	10.00	14.50	12.50	4.5
8	8.75	13.25	11.25	4.5
7	7.50	12.00	10.00	4.5
6	6.25	10.75	8.75	4.5
5	5.00	9.50	7.50	3.25
4	3.75	8.25	6.25	2.00
3	2.50	7.00	5.00	1.75
2	1.25	5.75	3.75	0.5

APPROVALS					DATE	
DRAWN		G.M.Chen		2015/7/17		
CHECKED						
APPROVALS						
TOLERANCES ARE		30~0.15 10~0.30 5~0.10 ~ 5		±0.30 ±0.20 ±0.15 ±2°		
ANGLE						
UNIT: mm		SCALE: 1:1		SHEET 1 OF 1		
DRAWING NO.				PROJ.		

No.	序号	名称	材料	数量	备注
Part Name		Material		Qty	Remark

NEW		DESCRIPTION.		CHANGE.	CHECK.	APPRO.
A						
REV.		DATE.				
ECN NO.						