


ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

技术要求 (Technical Index):




1. 材质与表面处理 (Material And Finish):
基座 (Housing) 和 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
2. 工作温度 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压 (Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压 (Withstanding Voltage): 200V AC/minute.



5PIN



SECTION A-A



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING		TITLE FPC连接器1.0间距5PIN翻盖下接H2.0 卧贴			
CHECKED					
APPROVED					
TOLERANCES ARE		PART NO.	LAIL-FPC-CX01-5P1.0-W	UNITS	mm
30-150	±0.35				
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG. NO.		Projection	
	±3°				