









REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



A



B



- Specifications()
- 1.Voltage rating():1500V DC
 - 2.Current rating():125A MAX
 - 3.Withstanding voltage():6800V DC
 - 4.Insulation resistance():200MΩ at DC1500V
 - 5.Protection level():IP67
 - 6.Mating cycles 500 cycles Min
 - 7.Recommended screw torque():
M4 0.8~1.0N.m
M5 3.4~4.0N.m
M6 4.5~5.5N.m
 - 8.Temperature range():-40 ~+125

KES-001 W V-M6 A

H5=φ5
B6=M6
M5=M5 ()
M6=M6 ()
A:A
B:B

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KES-001WV-M6A
APPROVED		SIZE: A4	DWG NO.: