




PCB Layout(Top View)

NOTE:  
1.Operating Force: 300gf $\pm$ 100gf  
2.Operation life: 10,000 Cycles.

|                |                    |         |       |                     |                                                                                       |              |                                                                                             |
|----------------|--------------------|---------|-------|---------------------|---------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------------|
| ⑥              | Spring             | ——      | 1     | SUS                 | Natural                                                                               | ——           |                                                                                             |
| ⑤              | Cover              | ——      | 1     | SUS                 | Natural                                                                               | ——           |                                                                                             |
| ④              | Knob               | ——      | 1     | PA6T                | Black                                                                                 | ——           |                                                                                             |
| ③              | Spring leaf spring | ——      | 2     | Phosphor bronze     | Ag Plated                                                                             | ——           |                                                                                             |
| ②              | Base               | ——      | 1     | PA6T                | Black                                                                                 | ——           |                                                                                             |
| ①              | Metal Terminal     | ——      | 6     | Phosphor bronze     | Ag Plated                                                                             | ——           |                                                                                             |
| ITEM           | PART NAME          | TER'NO. | QTY.  | MATERIAL            | FINISHING                                                                             | REMARK       |                                                                                             |
| APPROVALS      |                    |         | DATE  |                     |  |              |                                                                                             |
| DRAWN          |                    | LIUCAN  |       | 2024.12.3           |                                                                                       |              |                                                                                             |
| CHECKED        |                    |         |       | TITLE:              |                                                                                       |              |                                                                                             |
| APPROVALS      |                    |         |       | PUSHBUTTON SWITCHES |                                                                                       |              |                                                                                             |
|                |                    |         |       | PART NO.            |                                                                                       | K8-5852P-N1  |                                                                                             |
| TOLERANCES ARE |                    | 30~以上   | ±0.30 | ANGLE               | UNIT: mm                                                                              | SCALE: 1:1   | PROJ:  |
|                |                    | 10~30   | ±0.20 |                     |                                                                                       |              |                                                                                             |
|                |                    | 5~10    | ±0.15 |                     |                                                                                       |              |                                                                                             |
|                |                    | ~ 5     | ±0.10 |                     |                                                                                       |              |                                                                                             |
|                |                    | ±2'     |       | DRAWING NO.         | ——                                                                                    | SHEET 1 OF 1 |                                                                                             |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
|         |      |       |              |         |        |        |
|         |      |       |              |         |        |        |
|         | A    |       | NEW          |         |        |        |
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |