


Circuit Diagram

PCB Layout(Pattern side)

长脚左弯脚04#按柄

NOTE:
Rating: DC 30V 100mA
Operating Force: 50gf Max
Lifetime: 20,000 Cycles



⑦	Touch Point	—	1	Silver Alloy	Natural	—
⑥	Spring Plate	—	1	Beryllium copper	Natural	—
⑤	Terminal	—	3	Brass	Ag Plated	—
④	Housing	—	1	Nylon	Black	—
③	Cover	—	1	PBT	Black	—
②	Knob	—	1	PBT	White	—
①	Lever	—	1	SUS	Natural	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS				DATE					
DRAWN		LIUCAN		2023.5.22					
CHECKED						TITLE:		MICRO SWITCHES	
APPROVALS						PART NO.		K9-8227Y-L4DD-1B	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 		
		10~30	±0.20						
		5~10	±0.15						
		~ 5	±0.10						
		±2'		DRAWING NO.		_____		SHEET 1 OF	

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.