




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:−40°to+105°

Insulator Material:Polyester(UL94V-0)

Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30–60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PM1.0-2-1PU-Z	2*1	0.00	1.00
BX-PM1.0-2-2PU-Z	2*2	1.00	2.00
BX-PM1.0-2-3PU-Z	2*3	2.00	3.00
BX-PM1.0-2-4PU-Z	2*4	3.00	4.00
BX-PM1.0-2-5PU-Z	2*5	4.00	5.00
BX-PM1.0-2-6PU-Z	2*6	5.00	6.00
BX-PM1.0-2-7PU-Z	2*7	6.00	7.00
BX-PM1.0-2-8PU-Z	2*8	7.00	8.00
BX-PM1.0-2-9PU-Z	2*9	8.00	9.00
.....			
BX-PM1.0-2-20PU-Z	2*20	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PM1.0-2-NPU-Z	版本 REV.	A
			X.±0.30	X.°±5°	审核 CHECK	EVA		品名 TITLE	1.0FH H2.0 2xNPin 180度 W2.5 U型 PC2.0 6T	页次 SHEET	1/1
			.X±0.20	.X°±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.10	.XX°±0.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)		