


REV.	ECN NO.	DESCRIPTION	DRAW	DATE



5PIN

NOTE:

1. MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC(UL94V-0), COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC(UL94-V0).

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C} \sim +50^{\circ}\text{C}$.



STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

INSULATION RESISTANCE $>500\text{M}\Omega$.

WITHSTAND VOLTAGE: 200V/1 MINUTE.



SECTION A-A



Recommended FPC/FFC Dimensions

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		FPC连接器0.5间距5PIN翻盖式双侧触点上下接	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-FPC-CDX01-5P0.5-GW	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.		Projection		