











3D VIEW



P.C.B LAYOUT
TOP VIEW



Schematic

Rating: 1A 30V DC
Contact Resistance: 50 mΩ Max.
Operating temperature:-25℃~80℃
Operating force:3-30N
Operating Life:5,000cycles

③	SLEEVE	—	1	BRASS	Ni/Au Plating	—
②	Terminal	—	6	Phosphor bronze	Ni/Au Plating	—
①	Housing	—	1	PPA	Black	—
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®						
DRAWN		LIUCAN	2024.8.13								
CHECKED				TITLE:		PHONE JACKES					
APPROVALS				PART NO.		PJ-332G					
TOLERANCES ARE		30~以上	±0.30	ANGLE		UNIT: mm		SCALE: 1:1		PROJ: 	
		10~30	±0.20								
		5~10	±0.15								
		~ 5	±0.10								
				±2'		DRAWING NO.		_____		SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			