


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE




技术要求 (Technical Index):

1. 材质与表面处理 (Material And Finish):
基座 (Housing) and 盖子 (Cover): LCP UL94V-0 Nature Or Black;
端子 (Terminal): Phosphor Copper Au/Sn Plated;
焊片 (Solder): Copper Alloy Au/Sn Plated;
2. 工作温度 (Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压 (Rated voltage): 50V, AC/DC.
4. 额定电流: 0.4A, AC/DC.
5. 接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$.
6. 绝缘电阻 (Insulation resistance): $\geq 500\text{M}\Omega$.
7. 耐电压 (Withstanding Voltage): 200V AC/minute.

10PIN



SECTION A-A



PCB Layout

CUSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE FPC连接器0.5间距10PIN抽屉式下接（卧贴）		REV.	A
CHECKED					
APPROVED					
TOLERANCES ARE		PART NO. LAIL-FPC-BX01-10P0.5-W	UNITS mm		
30-150	±0.35			ANGLE ±3°	
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		DWG. NO.		Projection	