




P.C.B layout



Circuit Diagram



- NOTE:
- 1.Rating1:DC12V 3A
 - Rating2:48V DC/125V AC/250V AC 0.1A
 - 2.Operating froce:180gf MAX
 - 3.Electric Life:100,000
 - 4.Mechanical Life:500,000
 - 5.Ingress protection:IP67

⑧	Handle	—	1	SUS	—	—
⑦	Shrapnel	—	1	Brass	Plating silver	—
⑥	Contact	—	1	Ag	—	—
⑤	Sealed Circle	—	1	Silicone Rubber	—	—
④	Terminal	—	3	Brass(0.50t)	Plating silver	—
③	Plunger	—	1	POM	Black	—
②	Case	—	1	PA	Black	—
①	Cover	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	LIUCAN	2024.9.14				
CHECKED				TITLE:	MICRO SWITCHS	
APPROVALS				PART NO.	K9-2811N-0QDD	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			
		±2°		DRAWING NO.	PROJ: 	
					SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.