



ROHS

31PIN

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



When Actuator Is Opened
Scale 2:1

Note:

1.Material





- 1.1: Housing: LCP UL94-V0 Color:Natural.Or Black
- 1.2: Actuator: PA9T UL94-V0 Color:Black Or Natural
- 1.3: Contact: Phosphor Bronze.
- 1.4: LEG: Phosphor Bronze.

2.Plating

- 2.1: Contact: See Part Number.
- 2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
- 3.2: Current Rating: 0.2A AC/DC.
- 3.3: Operating Temperature: $-55^\circ\text{C} \sim +85^\circ\text{C}$.



RECOMMEND PCB LAYOUT

APPLICABLE FFC/FPC
FFC/FPC THICKNESS= 0.20 ± 0.03

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司	
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD	
CHECKED			
APPROVED			
TOLERANCES ARE		TITLE	FPC连接器0.3间距31PIN翻盖下接卧贴
30-150	± 0.35	PART NO.	LAIL-FPC-CX01-31P0. 3-GW
10-30	± 0.2	UNITS	mm
5-10	± 0.15	DWG. NO.	
0-5	± 0.1	Projection	