





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2026.03.19	
/	N/A		/	/	/



Specifications()
1.Voltage rating():750V DC
2.Current rating():
3.Withstanding voltage():3500V AC
4.Insulation resistance():100MΩ MIN at DC1000V
5.Protection level():IP67
6.Mating cycles 500 cycles Min
7.Temperature range():-40 ~+130



KMSD-211 W-200A-00
100
200

KMSD-211W-200A-00	400A	200A
KMSD-211W-100A-00	200A	100A

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.: KMSD-211W-200A-00
APPROVED		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE N/A
			PAGE 1/1
			REVISION A0