





ROHS



PCB LAYOUT

SPECIFICATION:

Current Rating: 3AMP

Temperature Range: -40°C to +105°C

Contact Resistance: 20mΩ Max

Insulation Resistance: 1000MΩ Min

Withstanding Voltage: AC 1000V

Material:

Insulator: Polyester (UL94V-0)

Standard: PA6T

Contact: Brass

Plating: Au over Ni

COSTOMTER DRAWING		LWLAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECKED							
APPROVED							
TOLERANCES ARE		TITLE		排针 PIN距2.54 塑高2.5 双排8PIN立贴	REV.	A	
30-150	+0.35	ANGLE	PART NO.		LAIL-PZ2. 54-8PX2-T	UNITS	mm
10-30	+0.2		DWG. NO.			Projection	
5-10	+0.15						
0-5	+0.1						