





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating: 3AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排针 PIN距2.54 塑高2.5 双排25PIN直插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PZ2.54-25PX2-L	UNITS	mm	
10-30	±0.2						
5-10	±0.15	±3°					
0-5	±0.1		DWG. NO.				
			Projection				