










MATED PAIR

NOTE :


I - HOUSINGS ARE KEYED TO ONLY ALLOW MATING WITH THE SAME COLOR HOUSING

spec ref				dr		Anooj-P Jacob	2024/03/18	Amphenol Power Solutions		MM		scale	1:1	size	A3
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Anooj-P Jacob	2024/03/18			ecn no					
ISO 406 ISO 1101				rv wr		-	-								
				appr		Varma Sudhir	2024/03/18	A Division of Amphenol Corporation		amphenol-icc.com		rel level: Released			
surface ISO 1302		linear		projection		title		IPC-M175 CONNECTOR ePwr™ BATTERY CONNECTOR		dwg no		10171426		rev A	
										cat. no.					
		ISO 1302		angular		0°		±2°		product family				Product - Customer Drw	


COLOR	PART NUMBER
GRAY	10171426-001LF
BLUE	10171426-002LF
RED	10171426-003LF



GRAY VOLTAGE KEYING



BLUE VOLTAGE KEYING



RED VOLTAGE KEYING

spec ref				dr		Anooj-P Jacob		2024/03/18		Amphenol Power Solutions				MM		scale		size											
tolerance std				eng		Anooj-P Jacob		2024/03/18						ecn no						1:1		A3							
ISO 406 ISO 1101				rvwr		-		-																					
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr		Varma Sudhir		2024/03/18		A Division of Amphenol Corporation				amphenol-icc.com				rel level: Released											
surface ISO 1302		linear		0.X ±0.5		0.XX ±		0.XXX ±		projection		title		IPC-M175 CONNECTOR ePwr™ BATTERY CONNECTOR						dwg no 10171426		rev							
																								cat. no.		-		A	
product family		-		Product - Customer Drw				sheet 2 of 2																					