





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating: 3AMP
Temperature Range: -40℃to+105℃
Contact Resistance: 20mΩ Max
Insulation Resistance: 1000MΩ Min
Withstanding Voltage: AC 1000V
Material:
Insulator: Polyester (UL94V-0)
Standard: PA6T
Contact: Brass
Plating: Au over Ni



PCB LAYOUT General±0.05mm.

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING							
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		排针 PIN距2.54 塑高2.5 双排15PIN直插	REV.	A
30-150	±0.35	ANGLE	PART NO.		LAIL-PZ2. 54-15PX2-L	UNITS	mm
10-30	±0.2						
5-10	±0.15	±3°	DWG. NO.			Projection	
0-5	±0.1						