





NOTE:
1.Rating1: 3A AC 125/250V
1.5A DC 30V
2.Operating froce: 110±30gf
3.Electric Life:10,000
4.Mechanical Life:1000,000
5.Ingress protection:IP67

⑧	Sealing mat	—	1	Silicone	—	—
⑦	Sealing cap	—	1	Silicone	—	—
⑥	Contact	—	3	Silver alloy	—	—
⑤	Shrapnel	—	1	Phosphor bronze	—	—
④	Terminal	—	3	Brass	Plating silver	—
③	Button	—	1	PBT	White	—
②	Cover	—	1	PBT	Black	—
①	Base	—	1	PBT	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK


APPROVALS			DATE		 hro®		
DRAWN		LIANG	2026.09.03				
CHECKED					TITLE:	MICRO SWITCHS	
APPROVALS					PART NO.	K9-2933N-DDBB	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2°		DRAWING NO.	_____		SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			











选型表

K9-2933A-PDDB-1A

开关系列	名称
K9	防水微动开关

编码	图示	产品规格
3		12.8*5.8*6.55(帽型导芯)

编码	电流规格	触点
3	3A 125/250V AC 1.5A 30V DC	银合金

编码	手柄类型	编码	手柄类型	编码	手柄类型
N	 00	D	 04	G	 16
A	 01	E	 05	H	 22
B	 02	F	 06	J	 114
C	 03			K	 07








编码	线材长度L	编码	线材长度L
O	无线材省略	C	250mm
A	150mm	D	300mm
B	200mm	其它	...

流水号	电线规格	流水号	电线规格
0	无线材省略	3	UL1007 22AWG 美标
1	UL1569 22AWG 美标	4	UL1007 24AWG 美标
2	UL1569 24AWG 美标	...	其他

编码	上盖颜色
B	黑色
W	白色
G	灰色

编码	底座颜色
B	黑色
W	白色
G	灰色

编码	触点类型
D	常开/常闭 SPDT
B	常开 SPST-NO
C	常闭 SPST-NC

编码	端子类型	编码	端子类型	编码	端子类型
P		D		T	
H		E			
L		F		W	
R		K	