

RoHS

REV.

ECN. #

DESCRIPTION

NAME

DATE



A0

—





NEW RELEASE

X. F. Wang

2023. 05. 12



SECTION: A-A

TOLERANCE: ± 0.05 , THICKNESS: 1.0~1.2mmRECOMMENDED PCB LAYOUT
(TOP VIEW)

NOTE:

1.MATERIAL:

1.1 HOUSING: LCP UL94V-0.

1.2 CONTACT: COPPER ALLOY T=0.20mm

1.3 SHELL: STAINLESS STEEL T=0.30mm

2.ELECTRICAL CHARACTERISTICS:

2.1 CONTACT RESISTANCE: 30mΩ Max

2.2 CONTACT CURRENT RATING: 1.5A

2.3 DIELECTRIC WITHSTANDING VOLTAGE: 100V AC R.M.S.

2.4 INSULATION RESISTANCE: 100MΩ Min

2.5 OPERATING TEMPERATURE: -40°C~75°C

2.6 RATE VOLTAGE: 30V DC

3 MECHANICAL CHARACTERISTICS:

3.1 INSERTION FORCE: 35N Max

3.2 EXTRACTION FORCE: INITIAL 10N Min, AFTER TEST 8N Min

3.3 DURABILITY: 5000 CYCLES

4.PLATING:

4.1 TERMINAL CONTACT: G/F(0.8u" Au) PLATING ON CONTACT AREA

80u" MIN Matte Tin PLATED ON SOLDER AREA


30u" MIN. Ni UNDERPLATED OVERALL

4.2 SHELL: 50u" MIN. NICKEL ALL OVER

5.SALT SPRAY: 24H

PIN NO.	1	2	3	4	
SIGNAL NAME	VBUS	D—	D+	GND	
REMARK	USB2.0 CONTACT PIN				
PIN NO.	5	6	7	8	9
SIGNAL NAME	SSRX—	SSRX+	GND	SSTX—	SSTX+
REMARK	USB3.0 CONTACT PIN				

104629432-X

H: BLACK HOUSING
L: BLUE HOUSING

3D VIEW

MILLIMETERS	INCH
X.° $\pm 2^\circ$	X.° $\pm 2^\circ$
.X ± 0.30	.X ± 0.012
.XX ± 0.20	.XX ± 0.008
.XXX ± 0.10	.XXX ± 0.004

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBiLai
Metal Plastic Technology Co., Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBiLai Metal Plastic Technology Co., Ltd


东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co., Ltd

TITLE	USB3.1 AF H=6.5 反向沉板 CH1.65	DR		
PART NO.	104629432-L	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE A4	SCALE 1:1	DIS NO.	UB012-000-X 客户图	


ROHS

Direction of use




NOTES:

- 1、Packing quantity per plate: 400PCS/Plate
- 2、Loading and packing method



3、Total packaging: 3200PCS/Box



Part Number	Description	Quantity
303020191	Carrierband (Lucent, PET W=32 PH=24)	79.1M
303040009	Box (K=K, T=7.0, 350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070014	Self-adhesive (W=25.50)	81.5M
303110001	Beam (K=K, T=7.0, 95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180021	REEL (BLUE, 13Inches*32mm, $\phi 330$)	8PCS
104629432-X	USB3.1 AF H=6.5反向沉板CH1.65	3200PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd				
X. ° $\pm 2^\circ$	X. ° $\pm 2^\circ$					
.X ± 0.30	.X ± 0.012					
.XX ± 0.20	.XX ± 0.008					
.XXX ± 0.10	.XXX ± 0.004					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd		TITLE	USB3.1 AF H=6.5反向沉板CH1.65		DR	
		PART NUM.	104629432-X		CHKD	
		PRO J.	PAGE	2/2	UNITS	mm
		SIZE	A4	SCALE	1:1	DIS NO.
						UB012-000-X客户图