









RECOMMENDED PCB LAYOUT (TOP VIEW)
GENERAL TOLERANCES: ± 0.05 ($t=1.6/1.2$)

NOTES:

1.MATERIAL

- 1.1 PLASTIC LCP,UL 94V-0,COLOR: BLACK
- 1.2 CONTACT:5P,C2680 4P,C5191
- 1.3 SHELL: STAINLESS STEEL



2.FINISH:

- 2.1 TERMINAL:50u" MIN. NICKEL PLATED OVERALL
- 2.2 CONTACT:SELECTIVE GOLD PLATED,
- 2.3 TAIL:100u" MATT-TIN PLATED
- 2.4 SHELL:50u" MIN. NICKEL PLATED OVERALL

3.PRODUCT SPECIFICATION REFER TO SP-A0669-01

4.PACKAGEDRAWING REFER TO PA0669-001

5.PRODUCT MUST CONFORM TO RoHS AND HALOGENFREE REQUIREMENT



Contact Number	SIGNAL NAME	MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
PIN1	VBUS	UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: USB 3.0 AF 180度插板 GEN2 版本 10G(H=13.35)		
PIN2	D-				PAR	USB-349-ARDW-L1.35	
PIN3	D+				DWN	Lucas	
PIN4	GND				CHKD	Ethan	
PIN5	StdA_SSXX-				APVD	Jacob	
PIN6	StdA_SSXX+	DECIMALS:	ANGLES:	SCALE: 1:1	UNIT: MM		
PIN7	GND_DRAIN	X.: ±0.50	X.*±3°	CUSTOMER COPY	SIZE: A4	SHEET: 1F1	REV: A
PIN8	StdA_SSTX-	X.X: ±0.30	X.X*±2°				
PIN9	StdA_SSTX+	X.XX: ±0.25	X.XX*±1°				
Shell	Shield						