




RoHS



Circuit Diagram

TOTAL HEIGHT					
Code	H	ø	Code	H	ø
038	3.8	2.15	060	6.0	2.05
043	4.3	2.15	065	6.5	2.05
045	4.5	2.15	070	7.0	2.00
050	5.0	2.10	075	7.5	1.95
055	5.5	2.10	080	8.0	1.95

Product No.: TS-008S-□-□-□-□

型号:

产品高度(H):

038=3.8mm
043=4.3mm
045=4.5mm

操作力度:

120=120gf±50gf
180=180gf±50gf
250=250gf±50gf

包装方式



-P=编带(非编带, 不启用)

弹片

D2=SUS/1PCS
D4=SUS/2PCS

脚距

(C68=L6.8) L1=7.5
(C75=L7.5) L1=8.5



PCB Layout(Pattern side)

⑦	Waterproof mat		1	Silica gel	Black
⑤	Terminal		4	Brass(0.3t)	Silvering
④	Reed		1	SUS	Silver plating
③	Button		1	PPA	Black
②	Cover		1	PPA	Black
①	Base		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	name	TS-008S-□-□-□-□
Approved	date	name	

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified


项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.35±0.1mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd									
design			date			name			TACT SWITCHS										
Review			date			model			TS-008S-□□-C□D□										
Approved			date																
number:																			
1:1		unit		mm		gape number				A4									