





Recommended P.C.B Layout

技术说明:

1. 材质: 黄铜, T=0.50MM
2. 表面处理: 镀镍
3. 表面无打点折痕批锋等
4. 适用于6×30mm 保险丝管
5. 额定电流: 15A
6. 未注公差按14级标准执行
7. 电镀后:
 - 1) 表面光泽无斑点;
 - 2) 镀层结合牢固无发泡现象;
 - 3) 盐雾试验48小时后无氧化不良。

APPROVALS			DATE	DEALON 德之隆®		
DRAWN	G.M.Chen	2015/5/22		ELECTRONICS CO.,LTD		
CHECKED				TITLE: FUSE HOLDER		
APPROVALS				PART NO. BX63532-05		
TOLERANCES ARE			30±0.15	±0.30	ANGLE	UNIT: mm
			10±0.20	±0.20		SCALE: 1:1
			5±0.10	±0.10	±2°	SHEET 1 OF 1
			~ 5	±0.10		PROJ. ①
ECN NO.	REV.	DATE.	DESCRIPTION.			
	A		NEW			
			CHANGE.			
			CHECK.			
			APPRO.			