








RECOMMENDEN PCB LAYOUT (TOP VIEW)
GENERAL TOLERANCES: ± 0.05 ($t=1.6/1.2$)

NOTE:

- MATERIAL:
 - 1.1 PLASTIC LCP,UL 94V-0, COLOR: BLACK
 - 1.2 CONTACT: C5191
 - 1.3 SHELL: STAINLESS STEEL
- FINISH:
 - 2.1 TERMINAL: 50μ " MIN. NICKEL PLATED OVERALL
 - 2.2 CONTACT: SELECTIVE GOLD PLATED, SEE TABLE A
 - 2.3 TAIL: 100μ " MATT-TIN PLATED
 - 2.4 SHELL: 50μ " MIN. NICKEL PLATED OVERALL
- PRODUCT SPECIFICATION REFER TO SP-A0669-01
- PACKAGE DRAWING REFER TO PA0669-001
- PRODUCT MUST CONFORM TO RoHS AND HALOGEN FREE REQUIREMENT



PIN NUMBER	SIGNAL NAME	MANUFACTURE DWG		东 莞 市 讯 普 电 子 科 技 有 限 公 司 DongGuan XunPu Electronics Co.,Ltd	
1	VBUS	UNLESS OTHERWISE SPECIFIED TOLERANCES			
2	D-				
3	D+				
4	GND				
5	StdA_SSRX-				
6	StdA_SSRX+	DECIMALS:	ANGLES:	TITLE: USB3.0 AF 180度插板无壳 边H=16.0 锡牌长1.35	
7	GND_DRAIN	X.: ± 0.50	$\pm 1^\circ$	PAR	USB-354-ARDW
8	StdA_SSTX-	X.X: ± 0.30		DWN	Lucas
9	StdA_SSTX+	X.XX: ± 0.20		CHKD	Ethan
Shell	Shield			APVD	Jacob
CUSTOMER COPY				SCALE: 1:1	UNIT: MM
				SIZE: A4	SHEET: 1F1
					REV: A