

A

B

C

D

E








F

G

H

I

J



SPECIFCATIONS:

Contact current Rating:

1.8 Amperes for pin1&pin4.

0.25 Amperes other contacts

Dielectric Withstanding Voltage: AC 100V(RMS)

Insulation resistance:100Megohms Minimum.

Contact Resistance:

30m Ω Max for pin1&pin4

50mΩMax for other contacts

Mechanical Characteristics:

Mating Force:35 Newtoms.Maximum

Unmating Force:10 Newtoms.Mlimum.

Operating Temperature:-40 °C+85 °C

					Pin Number	Signal Name	Pin Number	Signal Name	MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd				
ITEM	PART NAME	Material	Q'TY	REMARK					UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: USB 3.0 AF 侧贴直脚有卷边			
1	4P Semimanufactured Goods	Housing LCO&PBT	1	Black&Blue UL94V-0	1	VBUS	5	SSRX-				PAR	USB-376-ARSY		
2		Contact COPPER ALLOY	4	T=0.25 Plating Gild/Tin	2	D-	6	SSRX+	DWN	Lucas					
3	5P Semimanufactured Goods	Housing LCP&PBT	1	Black&Blue UL94V-0	3	D+	7	GND	DECIMALS:	ANGLES:		CHKD	Ethan		
4		Contact COPPER ALLOY	5	T=0.25 Plating Gild/Tin	4	GND	8	SSTX-	X.: ±0.50	±1°		APVD	Jacob		
5	Shell	Stainless Stell	1	T=0.3	SHELL	SHIELD	9	SSTX+	X.X: ±0.30		SCALE1:1	UNIT: MM			
									X.XX: ±0.20		CUSTOMER COPY		SIZE: A4	SHEET: 1F1	REV: A