

		D		E	
REV.	DESCRIPTION		ECN NO.	NAME	DATE






NOTES:

- 1.BASE: PA66
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

1. Spacing: 1.25
2. Voltage Rating: 125V AC DC
3. Current Rating: 1A AC DC
4. Insulation Resistance: 100M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 500V AC 1/Minute
7. Temperature Range: -25 $^{\circ}$ C ~ + 85 $^{\circ}$ C

Part No	Pin	A	B	C	D
WF-1A125A2P	2	1.25	4.40	3.20	
WF-1A125A3P	3	2.50	5.65	4.45	
WF-1A125A4P	4	3.75	6.90	5.70	2.50
WF-1A125A5P	5	5.00	8.15	6.95	3.75
WF-1A125A6P	6	6.25	9.40	8.20	5.00
WF-1A125A7P	7	7.50	10.65	9.45	6.25
WF-1A125A8P	8	8.75	11.90	10.70	7.50
WF-1A125A9P	9	10.00	13.15	11.95	8.75
WF-1A125A10P	10	11.25	14.40	13.20	10.00
WF-1A125A11P	11	12.50	15.65	14.45	11.25
WF-1A125A12P	12	13.75	16.90	15.70	12.50
WF-1A125A13P	13	15.00	18.15	16.95	13.75
WF-1A125A14P	14	16.25	19.40	18.20	15.00
WF-1A125A15P	15	17.50	20.65	19.45	16.25
WF-1A125A16P	16	18.75	21.90	20.70	17.50



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. .X ±0.20 .XX ±0.10 .XXX ±0.05 GENERAL ANGLE: X° ±5° X.X° ±3° X.XX° ±1°		TITLE: WAFER 1.25 直針						
		DWG. NO.: WF-1A125AXP			CHECKED: MAX			
		PART NO.: WF-1A125AXP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	