

		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	


NOTES:

- 1.BASE: PA66
2.PIN: Brass
3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C	D
WF-1A124A2P	2	1.25	4.40	3.20	
WF-1A124A3P	3	2.50	5.65	4.45	
WF-1A124A4P	4	3.75	6.90	5.70	2.50
WF-1A124A5P	5	5.00	8.15	6.95	3.75
WF-1A124A6P	6	6.25	9.40	8.20	5.00
WF-1A124A7P	7	7.50	10.65	9.45	6.25
WF-1A124A8P	8	8.75	11.90	10.70	7.50
WF-1A124A9P	9	10.00	13.15	11.95	8.75
WF-1A124A10P	10	11.25	14.40	13.20	10.00
WF-1A124A11P	11	12.50	15.65	14.45	11.25
WF-1A124A12P	12	13.75	16.90	15.70	12.50
WF-1A124A13P	13	15.00	18.15	16.95	13.75
WF-1A124A14P	14	16.25	19.40	18.20	15.00
WF-1A124A15P	15	17.50	20.65	19.45	16.25
WF-1A124A16P	16	18.75	21.90	20.70	17.50



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. .X ±0.20 .XX ±0.10 .XXX ±0.05 GENERAL ANGLE: X° ±5° X.X° ±3° X.XX° ±1°		TITLE: WAFER 1.25 直針					
		DWG. NO.: WF-1A125AXP		CHECKED: MAX			
		PART NO.: WF-1A125AXP		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL