



Notes:
Rated current:3.0A
Withstand Voltage:500V AC/DC
Contact Resistance:20mΩ Max
Insulation Resistance:1000MΩ Min
Operating Temperature:-40℃ TO +105℃
Contact Material:Brass
Plating:Gold Flash
Insulator Material: PA9T UL94V-0 BK

NO.	DATE	DESCRIPTION	APPROVAL	DRAWING:	GENERAL TOLERANCE	
1	2024-06-20	初次发行	Jack	MAO ZI HAO	.X: ±0.30 .XX: ±0.20 .XXX: ±0.10	.X*: ±2° .XX*: ±1° .XXX*: ±0.5°
2				CHECKED:	UNIT: MM SCALE: N/A SHEET: 1/1 PROJECTION	
3				YAO HUI SONG		
4				APPROVAL:		
5				HAN XIAO QIU		

东莞市文章济美电子有限公司	
DESCRIPTION: 2.54x2.5 2xNP PA6.0 PC3.0 L11.6	
PART NO:	REC:1.0
SERIES :	ROHS