






序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2




2PIN

说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: LCP UL94V-0, 颜色: 本色;
3. 焊片: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
4. 接触针: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流: 2A AC/DC
8. 额定电压: 100V AC/DC
9. 接触阻抗: 10mΩ Max.
10. 绝缘阻抗: 1000MΩ Min.
11. 耐电压: 800V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
HY2.0-2PWT	2	2.00	8.00	4.80
HY2.0-3PWT	3	4.00	10.00	6.80
HY2.0-4PWT	4	6.00	12.00	8.80
HY2.0-5PWT	5	8.00	14.00	10.80
HY2.0-6PWT	6	10.00	16.00	12.80
HY2.0-7PWT	7	12.00	18.00	14.80
HY2.0-8PWT	8	14.00	20.00	16.80
HY2.0-9PWT	9	16.00	22.00	18.80
HY2.0-10PWT	10	18.00	24.00	20.80
HY2.0-11PWT	11	20.00	26.00	22.80
HY2.0-12PWT	12	22.00	28.00	24.80
HY2.0-13PWT	13	24.00	30.00	26.80
HY2.0-14PWT	14	26.00	32.00	28.80
HY2.0-15PWT	15	28.00	34.00	30.80
HY2.0-16PWT	16	30.00	36.00	32.80
HY2.0-17PWT	17	32.00	38.00	34.80
HY2.0-18PWT	18	34.00	40.00	36.80
HY2.0-19PWT	19	36.00	42.00	38.80
HY2.0-20PWT	20	38.00	44.00	40.80



PCB LAYOUT

TOL.: ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PHB-SMT-AW	
DECIMALS:		PAR	HY2.0-XPWT
X.:±0.30		DWN	Lucas
X.X:±0.25		CHKD	Ethan
X.XX:±0.20		APVD	Jacob
ANGLES:		SCALE 1:1	UNIT:MM
X.:±5°		SIZE:A4	SHEET:1F1
X.X':±3°		CUSTOMER COPY	REV:A
X.XX':±1°			